

SK TIE4-HAN4A-K-LE-MX

Part number: 275 274 117

Power input connection extension



Scope of delivery

1 x	Adapter plate with seal
1 x	Housing attachment HAN 3A
1 x	Pin insert (M) HAN 4A
3 x	Connecting line
1 x	Earthing line



Field of use

Connection extension with a plug-in mains voltage connection (power input) directly mounted on the inverter (or motor adapter) or on the motor terminal box with a HAN 4A plug connector. Four power connections (+PE) and an M16 threaded hole is available.



Technical Information / Datasheet	SK TIE4-HAN4A-K-LE-MX			
Connection extension	TI 275274117	V 1.1	3614	EN

Technical data

Plug connector type	HAN 4A (pin)
Number of contacts	4 +PE
Cable cross-section	0.75 ... 2.5 mm ²
Rated current	10 A
Rated voltage	250 V
Contact insert	Pin insert (M)
Version	straight
Protection class	IP65

Connections

HAN 4A PIN	Potential	SK 135E ... 175E Terminal	SK 180E ... 190E Terminal	SK 2xxE Terminal
1	L1	L1	L1	L1
2	L2	L2	L2	L2
3	L3	L3	L3	L3
PE	PE	PE	PE	PE

Optional accessories (not contained in the article)

HAN 4A (female) - (Counterpart to the installed plug connector)

Number	Designation	Manufacturer	Information
1 x	Sleeve housing HAN 3 A	Harting	e.g. Harting order number: 19 20 003 1440
1 x	HAN 4A-F-QL 1,5 mm ² Quick-Lock	Harting	Harting order number: 09 20 004 2734
1 x	HAN 3A fastening screw	Harting	Harting order number: 09 20 000 9918
1 x	Cable gland SKINDICHT SKZ-M M20 x 1.5, 13-15 mm	LAPP Kabel	52106830

Additional documentation and software (www.nord.com)

Document	Designation
BU_0135	Manual for Motor Starters SK 135E, SK 175E
BU_0180	Frequency Inverter Manual for SK 180E, SK 190E
BU_0200	Manual for Frequency Inverters SK 2xxE