# **GETRIEBEBAU NORD**

Member of the NORD DRIVESYSTEMS Group



Getriebebau NORD GmbH & Co. KG Getriebebau-Nord-Straße 1 • 22941 Bargteheide, Germany • www.nord.com

## SC P4GA14 HQ4SPF OE xxx UL

#### **Cable Power Mains**

#### Scope of supply

NORD Cable
Preconfigured for connection via one power plug.

Name	p/n	Length
SC P4GA14 HQ4SPF OE 1.5 UL	275 274 240	1.5 m
SC P4GA14 HQ4SPF OE 3 UL	275 274 241	3.0 m
SC P4GA14 HQ4SPF OE 5 UL	275 274 242	5.0 m



#### Field of use

This cable is usable for the following application:

Mains incoming voltage supply (3-phase + PE)

### **Necessary inverter conditions**

The frequency inverter must be equipped with following power plug:

Mains incoming power plug HAN Q4/2

It only is allowed for qualified electricians to install and commission the module. An electrician is a person who, because of their technical training and experience, has sufficient knowledge relating to

- · switching on, switching off, isolating, earthing and marking power circuits and devices,
- proper maintenance and use of protective devices in accordance with defined safety standards.

# A DANGER!

### Danger of electric shock

The frequency inverter continues to carry hazardous voltages for up to 5 minutes after it was switched off.

• Work must not be carried out unless the device has been disconnected from the voltage and at least 5 minutes have elapsed since the mains was switched off!

# 1 Information

## **UL category (PVVA2)**

This cable fulfils the requirements of the UL category PVVA2. The cable is mounted with UL listed components and is produced under the UL "Wiring Harness Program" (Category ZPFW2/8) at a certified production site. The cable gets a special UL "Wiring Harness" traceability label (Category ZPFW2).

USUE NO. 0 0 0 0 0 0 FORM N 1 PCS

Example of identification mark

Technical Information / Datasheet	ormation / Datasheet SC P4GA14 HQ4SPF OE xxx UL		L	
Specification of connection cable	TI_275274240-242	3.0	3820	en



## **Technical Data**


Specification	Plug Power OUT	
Number of contacts	4 + PE	
Type of contact	Male (M)	
Housing type	Straight	
Housing material	Plastic	
Rated current IN	12 A (UL)	
Rated voltage	600 V (UL)	
Pollution degree	3	

Specification	Mains	
Cable preparation	Not stripped	

Specification	<b>Cable (68)</b>		
AWM Style	2587		
Designation	14AWG		
Bending radius	4x cable diameter		
Outside diameter	approx. 10.8 mm		
Operation temperature	-25° +75 °C		
Rated voltage	600 V (EU)		
Installation type	Fixed laying		
Jacket material	PVC		
Jacket colour	Grey (RAL 7001)		
Cable shield	No		
Drag chain compatibility	No		
Halogen-free	No		
Flammability test acc. to	FT4		

## PIN assignment

Potential	PIN assignment Electronics	(Cable colour) designation acc. to AWM Style		Flying lead Mains connection
L1	1	(Black) 1		Single wire
L2	2	(Black) 2		Single wire
L3	3	(Black) 3		Single wire
	GNYE	(Green- Y	rellow)	Single wire



2 / 2 TI\_275274240-242 - 3820