GETRIEBEBAU NORD

Member of the NORD DRIVESYSTEMS Group



Getriebebau NORD GmbH & Co. KG
Getriebebau-Nord-Straße 1 • 22941 Bargteheide, Germany • www.nord.com

CABLE PLUG (F) M12-08 L= xxM

Cable IG-IGx1P

Scope of supply

1	Х	M12 plug (M), 8-poles, straight,	
1	Х	Cable with 8 single wires, shielded, twisted pair	

Part number	Cable length			
1955 1580	2 m			
1955 1581	5 m			
1955 1582	10 m			
1955 1583	15 m			
Incremental encoder cable for NORD option: "IGx1P" / "IGx1P8" with 8-poles M12 plug				



It only is allowed for qualified electricians to install and commission the module. An electrician is a person who, because of their technical training and experience, has sufficient knowledge relating to

- · switching on, switching off, isolating, earthing and marking power circuits and devices,
- proper maintenance and use of protective devices in accordance with defined safety standards.

A DANGER!

Danger of electric shock

The frequency inverter continues to carry hazardous voltages for up to 5 minutes after it was switched off.

• Work must not be carried out unless the device has been disconnected from the voltage and at least 5 minutes have elapsed since the mains was switched off!


Field of use

Incremental encoder cable connects the electronic device with the NORD motor via "IGx1P" or "IGx1P8" motor option. The "IGx1P" / "IGx1P8" option is equipped with 8-poles standard plug.

Technical Information / Datasheet	Kabel IG-IGx1P (OE-IG-A8F gerade)		F	
Specification of connection cable		1.0	3519	en



Female



Inverter connection Encoder connection

1 Information

Fixed laying system for the cable

This cable is only useable for stationary (not moved) installation. All values for the fixed laying system are noted on this data sheet. Other laying systems are not allowed with this cable type.

Technical Data

M12 plug	Specification	
Contact quantity 8-poles		
Coding A – coded		b
Contact type	Female (F)	
Screw M12x1	Nut	
Construction type	Straight	
Protection (screwed)	NEMA 1,3,4,6P	IP68
Breakaway torque 0,6		
Pollution degree	3	

Cable	Specification
Braid shield coverage	26 AWG, braided shield
Material	Tinned copper

Cable	Specification		
AWM Style	20233		
Jacket material	PUR		
Jacket color	Grey		
Outside diameter	7.2 mm (+/- 0.28)		
Bending radius	10x cable diameter		
Wire cross section	4x 2x 0.25 mm ²		
Wire isolation	PVC		
General information			
Operating voltage	max. 60 V DC		
Operating current	max. 2 A		
Operating temperature	-10 + 80°C		
Flammability test	FT1		

PIN assignment:

Function	Cable color		Open wires	Schematic diagram	PIN Female (F) electronic
GND 0V	White		Wire end sleeve		1
+Ub	Brown		Wire end sleeve		2
Spur "A"	Green		Wire end sleeve		3
Spur "A \"	Yellow		Wire end sleeve		4
Spur "B"	Grey		Wire end sleeve		5
Spur "B \"	Pink		Wire end sleeve		6
Spur "0"	Blue		Wire end sleeve		7
Spur "0 \"	Red		Wire end sleeve		8

2 / 2 --- 3519