GETRIEBEBAU NORD

Member of the NORD DRIVESYSTEMS Group



Getriebebau NORD GmbH & Co. KG
Getriebebau-Nord-Straße 1 • 22941 Bargteheide, Germany • www.nord.com

SC P4G2.5 HQ4SPF OE xxx

Cable Power Mains

Scope of supply

| NORD Mains Cable |
|--|
| Preconfigured for connection via one power plug. |

| Name | p/n | Length |
|-------------------------|-------------|--------|
| SC P4G2.5 HQ4SPF OE 1.5 | 275 274 840 | 1.5 m |
| SC P4G2.5 HQ4SPF OE 2 | 275 274 839 | 2.0 m |
| SC P4G2.5 HQ4SPF OE 3 | 275 274 841 | 3.0 m |
| SC P4G2.5 HQ4SPF OE 5 | 275 274 842 | 5.0 m |
| SC P4G2.5 HQ4SPF OE 10 | 275 274 843 | 10.0 m |



Field of use

The mains incoming cable is useable for the following application:

Mains voltage supply

(with flying lead)

Necessary inverter accessory:

The electronic device must be equipped with the plug type below:

Mains incoming plug

HAN Q4/2 (Male)

It only is allowed for qualified electricians to install and commission the module. An electrician is a person who, because of their technical training and experience, has sufficient knowledge relating to

- switching on, switching off, isolating, earthing and marking power circuits and devices,
- proper maintenance and use of protective devices in accordance with defined safety standards.

A DANGER!

Danger of electric shock

The frequency inverter continues to carry hazardous voltages for up to 5 minutes after it was switched off

• Work must not be carried out unless the device has been disconnected from the voltage and at least 5 minutes have elapsed since the mains was switched off!

| Technical Information / Datasheet | SC P4G2.5 HQ4SPF OE xxx | | | |
|-----------------------------------|-------------------------|-----|------|----|
| Specification of connection cable | TI_275274839-843 | 3.0 | 3820 | en |



Technical Data


| Specification | Plug Electronic | | |
|------------------------------|-----------------|--|--|
| Number of contacts | 4 + PE | | |
| Type of contacts | Female (F) | | |
| Housing type | Straight | | |
| Housing material | Plastic | | |
| Rated current I _N | 12 A | | |
| Rated voltage | 400 V (EU) | | |
| Pollution degree | 3 | | |

| Specification | Mains Connection | | |
|------------------|------------------|--|--|
| Cable gland | Without | | |
| Cable dismantled | No | | |
| Wires equipped | Not prepared | | |

| Specification | Cable (60) | |
|---------------------------|-------------------------------|--|
| Standard | DIN EN 50525-2-51 | |
| Designation | 2,5 mm ² | |
| Bending radius | 4x cable diameter | |
| Outside diameter | approx. 9.3 mm | |
| Operation temperature | -40 up to +80 °C | |
| Rated voltage | 300/500 V (U ₀ /U) | |
| Installation type | Fixed laying | |
| Jacket material | PVC | |
| Jacket colour | Grey (RAL 7001) | |
| Cable Shield | No | |
| Drag chain compatibility | No | |
| Halogen-free | No | |
| Flammability test acc. to | DIN EN 60332-1-2 | |

PIN assignment

| Potential | PIN assignment Electronics | (Cable colour) designation acc. to DIN VDE 0293 | | Flying lead Mains connection |
|-----------|-------------------------------|---|---------|---------------------------------|
| L1 | 1 | (Black) 1 | | Single wire |
| L2 | 2 | (Black) 2 | | Single wire |
| L3 | 3 | (Black) 3 | | Single wire |
| | GNYE | (Green- | Yellow) | Single wire |



2 / 2 TI_275274839-843 - 3820