# **GETRIEBEBAU NORD**

Member of the NORD DRIVESYSTEMS Group




Getriebebau NORD GmbH & Co. KG Getriebebau-Nord-Straße 1 • 22941 Bargteheide, Germany • www.nord.com

## SK BRI4-1-200-100

Internal braking resistor for connection to a NORDAC FLEX SK 2xxE

Part number: 275 272 008



Only qualified electricians are allowed to install and commission the module. An electrician is a person who, because of their technical training and experience, has sufficient knowledge with regard to

- switching on, switching off, isolating, earthing and marking power circuits and devices,
- proper maintenance and use of protective devices in accordance with defined safety standards.

# $\mathbf{A}$

## **DANGER!**

## Danger of electric shock

The frequency inverter continues to carry hazardous voltages for up to 5 minutes after it was switched off.

• Work must not be carried out unless the device has been disconnected from the voltage and at least 5 minutes have elapsed since the mains was switched off!



## **CAUTION**

## Danger of burns

The module and all other metal components can heat up to temperatures above 70 °C.

Sufficient cooling time must be allowed for when working on the components in order to avoid injuries (local burns) to parts of the body coming into contact with the components.

In order to avoid damage to neighbouring objects, sufficient clearance must be maintained during installation.

### NOTICE

## Validity of this document

This document is only valid in combination with the operating instructions for the relevant frequency inverter. Safe commissioning of this module and the frequency inverter depends on the availability of this information.

Technical Information / Datasheet SK BRI4-1-200-100		-100		
Brake resistor	TI 2752272008	1.0	3018	en



## Scope of delivery


Mod	Module		
1 x	Braking resistor	SK BRI4-1	
1 x	Fastening screw	M4 x 12 hexagon socket screw	
1 x	Washer	A 4.3	
1 x	Adapter plate	Aluminium, 4 mm	
1 x	Heat conducting film	Thermo-silicone, 0.3 mm	



### Field of use

Dynamic braking (frequency lowering) of a three-phase motor via a frequency inverter results in generator braking energy that – depending on the particular application – is dissipated by a braking resistor. This superfluous energy is transformed into heat.

The internal braking resistor is designed for the NORDAC *FLEX* SK 200E series of units and depends on the mains voltage and the power. The internal braking resistor can be used for applications in which only slight, short braking phases are to be expected.



#### **Technical Data**

## Electrical data

Number of leads		2
Resistance	Ω	200

Max. continuous power P <sub>n</sub> 1)	W	100
Energy consumption P <sub>max</sub> 2)	kWs	1.0

<sup>&</sup>lt;sup>1)</sup> Reduction of the continuous power of the braking resistor to 25 % of the rated power.

#### General

Temperature range	°C	- 40 + 200
Tightening torque		
Screw	Nm	2.5 - 3.0
Weight	kg	0.08

Certifications	CE, RoHS, UL
Protection class	IP00
Mounting 1)	
Hexagon socket screw	M4 x 12

<sup>1)</sup> The screw and the washer are included in the scope of delivery

2 / 6 TI 2752272008 - 3018

 $<sup>^{2)}\,\</sup>mbox{The}$  stated value applies to a single use within 10 s.



## **Dimensions**

Housing dimensions		
Total [mm]	WxHxD	61.0 x 44.0 x 5.8
Adapter plate [mm]	WxHxD	60.0 x 40.0 x 4.5
Heat conducting	WxHxD	55.0 x 44.0 x 0.3
film [mm]		
Resistance [mm]	WxHxD	61.0 x 41.0 x 1.0
Cable / line [mm]		
Lead black / black	L	60.0 / 60.0
Wire end sleeve	L	8.0





### Connections

Name	+B	-В	
Cross section / type	AWG 20		
Wire colour	Black Black		
Terminal label	Power terminal +B	Power terminal -B	
Tightening torque			
SK 2xxE	1.2 – 1.5 Nm		

# **i** Information

## **Versions**

Due to the production process, various versions of braking resistor are available for installation and connection to  $NORDAC\ FLEX$  frequency inverters.



Older version



**Current version** 

TI 2752272008 - 3018 3 / 6



## Frequency inverter assignment

## **1** Information

## Overview in the manual

The braking resistors provided by the NORD DRIVESYSTEMS Group are specially designed for the particular frequency inverters.

Otherwise, the internal braking resistor and the frequency inverter may be damaged during operation.

For detailed information, please refer to section  $\square$  Assignment of Braking Resistors, in the relevant frequency inverter manual  $\square$  "Further documentation and software: www.nord.com".

#### Installation

Installation location	Direct installation and connection to a decentralised NORDAC FLEX frequency inverter:	
	In the connection unit of the frequency inverter	
Installation orientation	Option slot 2	
Fastening	With screws (fastening material is included)	

## **1** Information

## Assembly sequence

To install or remove the internal braking resistor, a power terminal strip which must be removed from the connection unit.

For the use of Type SK CU4-... customer interfaces and depending on the type of device and the options used, further components may need to be removed.

With the motor mounted version, the motor cover / insulating plate must be correctly removed. In contrast, for a wall mounted version, no motor cover / insulating plate is installed in the connection unit.



For detailed information regarding installation of the connection unit and the optional modules, please refer to section  $\square$  Assembly and Installation, in the frequency inverter manual  $\square$  "Further documentation and software: www.nord.com".

## Installation steps


- Installing the frequency inverter
   The SK 2xxE frequency inverter has not yet been installed on the SK TI4 connection unit and the drive.
- 2. Installing the internal braking resistor
  The braking resistor is fastened to option slot 2 in the SK T14 connection unit.
  - All components are installed in the connection unit using the enclosed M4 hexagon socket screw and the washer.



Motor mounted version

4 / 6 TI 2752272008 - 3018





# **1** Information

## Peak load limitation - DIP switch (S1)

If a type SK BRI4-...internal braking resistor is used, the DIP switch (S1) DIP No., 8 see "Further documentation and software: www.nord.com", must be set to "On". This is important in order to activate a peak power limitation to protect the braking resistor.

TI 2752272008 - 3018 5 / 6



#### **Parameters**


For optimum operation of the internal braking resistor, no parameters of the frequency inverter need to be changed. Limitation of the peak load is carried out solely via the hardware using DIP switch S1 with DIP No. 8 set to the position "On". Refer to the frequency inverter manual for details "Further documentation and software: www.nord.com".

## **Error messages**

Error messages of the internal braking resistor – the current or the archived message of the last fault – can be retrieved using the information parameters Actual fault P700 and Last fault P701 from the error memory of the frequency inverter. Refer to the frequency inverter manual for details "Further documentation and software: www.nord.com").

Error (E030/E050)	Meaning	Remarks
3.1	I <sup>2</sup> t overcurrent limit	Brake chopper: I <sup>2</sup> t limit has been triggered, 1.5x value for 60 s reached  • Avoid overcurrent in brake resistance
5.0	Overvoltage UZW	Link circuit voltage too high  Check the function of the connected braking resistor (broken cable)  Resistance value of connected braking resistor too high

## Wiring diagram



## Further documentation and software: www.nord.com

Document	Designation	
<u>BU 0200</u>	SK 200E frequency inverter manual	

6 / 6