



SK ① Gear Unit ② Shaft/Mounting ③ Reducer Options - ④ Input/Motor Motor Options

①	Gear Unit 072.1 172.1 372.1 373.1 572.1 573.1 672.1 673.1 772.1 773.1 872.1 873.1 972.1 973.1		②	Shaft/Mounting <input type="checkbox"/> - Footed <input type="checkbox"/> F - B5 Flange • B5 Flange Diameter <input type="text"/>		<input type="checkbox"/> Z - B14 Flange <input type="checkbox"/> XZ - Foot/B14 Flange <input type="checkbox"/> XF - Foot/B5 Flange • XF Flange Diameter <input type="text"/>	
				③	Reducer Options <input type="checkbox"/> VL - Heavy Duty Output Bearings <input type="checkbox"/> AL - Axial/Thrust Output Bearings <input type="checkbox"/> PR - Flange Pilot Removal <input type="checkbox"/> FKM - Fluoro Rubber Seals <input type="checkbox"/> SWV - Special Solid Shaft <input type="checkbox"/> SM5 - Stainless Steel Output Shaft		<input type="checkbox"/> OSG - Oil Sight Glass <input type="checkbox"/> OA - Oil Expansion Chamber <input type="checkbox"/> LL - Long Term Storage <input type="checkbox"/> MDP - Magnetic Drain Plug <input type="checkbox"/> ADP - Additional Drain Plug

④	Input Shaft	NEMA Adapter	IEC	Integral Motors	Integral Premium Efficient Motors		Integral Intermittent Duty (60 min) Motors	
					W	N56C N140TC N180TC N210TC N250TC N280TC N320TC	IEC 63 IEC 71 IEC 80 IEC 90 IEC 100 IEC 112 IEC 132 IEC 160 IEC 180 IEC 200	63S/4 - 0.16hp 63L/4 - 0.25hp 71S/4 - 0.33hp 71L/4 - 0.50hp 80S/4 - 0.75hp
					Other Speeds Available		Other Speeds Available	

Product Specifications

Ratio <input type="text"/> :1 — OR — Output Speed <input type="text"/> rpm	Mounting Position <input type="radio"/> M1 <input type="radio"/> M2 <input type="radio"/> M3 <input type="radio"/> M4 <input type="radio"/> M5 <input type="radio"/> M6 <input type="radio"/> Special _____		Paint <input type="radio"/> No Paint (Standard) <input type="radio"/> Stainless Steel Paint <input type="radio"/> NSD+ (gray) <input type="radio"/> NSD+W (white) <input type="radio"/> NSD-X3 (gray) <input type="radio"/> NSD-X3W (white) <input type="radio"/> Special _____	Lubricant <input type="radio"/> Standard <input type="radio"/> Synthetic <input type="radio"/> Food Grade <input type="radio"/> Other _____
--	---	--	---	--

Shaft Diameter

Gearmotor Only Details

Voltage & Frequency <input type="radio"/> 230/460V-60Hz <input type="radio"/> 575V-60Hz <input type="radio"/> 208V-60Hz <input type="radio"/> 400V-50Hz <input type="radio"/> 115/230V-60Hz, 1 ph. <input type="radio"/> Other _____	Terminal Box Pos. <input type="radio"/> TB1 <input type="radio"/> TB2 <input type="radio"/> TB3 <input type="radio"/> TB4		Conduit Entry Loc. <input type="radio"/> CE I * <input type="radio"/> CE II <input type="radio"/> CE III * <input type="radio"/> CE IV * Brakemotor	
---	--	--	---	--

Mtg. Pos. M1 Shown

Mtg. Pos. M1 Shown