

## Technical Information / Datasheet

### SK TIE4-M12-CAO

Part number: 275 274 501

CANopen connection extension  
M12 BUS system connector



#### Scope of delivery

1 x	M12 Plug connector	SK TIE4-M12-CAO
1 x	Cover cap	grey

As-delivered status with screwed-on connector cover



#### Field of use

The M12 Plug connector has open cable ends and wire end sleeves. It is used to make a pluggable connection using normal commercial M12 round plug connectors. It connects the CANopen technology option with the incoming CANopen field bus cable at the input side.

#### Technical data

Version	
Temperature range	-30 ... +90 °C
Contact insert Colour / Material	Grey / RAL 7042 Plastic
Round plug connector Material	Metal, CuZn, nickel plated
Connection / Type Round plug connector	M12x1, adjustable Plug connector with flexible strand M16x1.5, metric screw thread
Contact insert Contacts / Coding	5 pin, A - coded

Weight	23 g
Connector cover Colour / Material	Grey / RAL 7042 Plastic
Protection class (screwed)	IP67
Fastening	Hexagonal nut M16x1.5 *
Tightening torques * M12x1 Male socket connector M16x1.5 Screw thread	0.6 Nm 1.5 Nm


\* Suitable assembly spanner commercially available (see Installation)

Cable	
Number of conductors / Cross section	5 x 0.34 mm <sup>2</sup>
Wire strands / colours	UL / (wt, br, bl, bk, gr)
Length of wire strands	250 mm
Degree of fouling	3 / 2

Mech. Service life	min. 100 plugging cycles
Operating voltage	max. 60 V
Current rating	4 A
Insulation resistance	≥ 10 <sup>8</sup> Ω




Connection extension				SK TIE4-M12-CAO	
1.2	Extensive revision	2414	Bch	TI 275274501	EN
<b>version</b>	<b>reason for change(s)</b>	<b>issue</b>	<b>name</b>	<b>document</b>	<b>speech</b>

### Circuit diagram



### Installation / option locations




The M12 Receptacle connector are intended for direct installation in a free M16 hole / threaded opening of the device series (see below).









Device series	Recommended option location	Option locations
<b>SK 135E *</b> <b>SK 180E * ... SK 190E *</b> Housing SK 1xxE xxx-xxx-x (-C)	4R / 4L (incoming) 5R / 5L (outgoing)	
<b>SK 200E</b> Frequency inverter connecting unit SK TI4-x-2xx-x (-C)	4R / 4L (incoming) 5R / 5L (outgoing)  optional ** 6R / 6L, 7R / 7L, 8R / 8L	
<b>BUS technology box</b> BUS connection unit SK TI4-TU-BUS (-C)	1 / 2 / 3 / 4  optional *** 5R / 5L	
* The configuration capability of the respective Receptacle connector depends on its functionality with regard to the device series, e.g. the SK TIE-M12-SH Socket connector cannot be installed with the SK 1xxE housing. ** Size 1 – 3 with optional SK TIE4-M12-M16 connection extension, size 4 direct installation *** With optional SK TIE4-M20-M16 connection reduction		

The installation position and mounting location (coding pin or coding groove on contact carrier) of the Socket connector is freely positionable and should be aligned (see installation step 6) such that angled M12 round connectors can also be connected in a way that avoids collisions.

The installation steps described in the following apply to the installation of the M12 Receptacle connectors in the housing and in the frequency inverter connecting unit or the BUS connecting unit of an external technology box.

#### Installation steps for installation of the M12 Receptacle connector

1.	Remove M16 blind plug at the provided option location side (right / left) of the starter or frequency inverter housing or the connection unit.	
	Remove M16 blind plug from the provided option location hole (bottom) of the BUS connection unit.	
2.	Screw the middle hexagonal nut towards the front using a size 17 open-ended spanner.	

3.	<p><b>EMC</b> Twist associated wire pairs together (e. g. bus system, power supply, etc.).</p>		
4.	<p>Screw M12 flanges component directly into the affected M12 threaded opening of the housing or connecting unit of the frequency inverter. Screw M12 Receptacle connector into the relevant M16 threaded opening of the BUS connecting unit.</p>		
<p><b>Alternative option locations</b> Connection extension <b>SK TIE4-M12-M16</b> The M12 Receptacle connector can alternatively be installed with an <b>optional</b> M12-M16 connection extension. First screw the M12 Receptacle connector directly into the connection extension and then fit into the M12 threaded opening in the connection unit. For more information see Optional accessories</p>			
<p>Connection reduction <b>SK TIE4-M20-M16</b> The M12 Receptacle connector can alternatively be installed with an <b>optional</b> M20-M16 connection reduction. First screw the M12 Receptacle connector directly into the connection reduction and then fit into one of the side M12 threaded openings in the connection unit. For more information see Optional accessories</p>			
5.	<p>Align coding pin / coding groove vertically to 12 o'clock by rotating the front hexagonal nut.</p>	<p>Socket connector</p> 	<p>Plug connector</p> 
6.	<p>Secure the front hexagonal nut with a 17 mm open-ended spanner. Screw the rear hexagonal nut to the connection unit or the starter or frequency inverter housing using a size 17 open-ended spanner or a special torque / installation wrench. Take the specified <b>tightening torques</b> into consideration, see technical data.</p>		
7.	<p>Ensure that the M12 round plug connector or the cover cap is properly screwed onto the M12 Receptacle connector and tightened.</p>		

**NOTICE**

**Corrosion**

Pay attention to leaktightness during the installation of all components (assembly, connection extension etc.). It must be ensured that all components are correctly seated and the tightening torques are adhered to when doing this.

In order to ensure that protection class **IP66** is complied with (concerns all devices with type key SK ...-C), another **pressure - leaktightness test** must be performed when the assembly work has been completed.

Failure to do this will allow moisture to penetrate the device, which will result in the risk of corrosion and short circuiting.

**i Information**

**Torque / assembly wrench**



In order to provide a secure, sealed and vibration-proof connection, the M12 connection extensions, which are equipped with a hexagonal threaded ring (size 17), should be tightened with special torque / assembly wrenches. For professional installation NORD recommends the use of commercially available assembly tools (M12, size 17) with an adjustable, defined tightening torque (e.g. from Murrelektronik).

**Connections**

The open cable ends of the extension / M12 Plug connector are connected to the terminal strip of the BUS connection unit (technology box) or the BUS customer interface in the frequency inverter (see below).



<b>BUS connection unit</b> SK TI4-TU-BUS (-C)	<b>BUS technology box</b> SK TU4-CAO (-M12) / (-C)	<b>BUS customer interface</b> SK CU4-CAO
--	---	---

**Electrical connections**

<p>Contact assignments 5-pole Plug connector A-coded</p>	<b>Connection extension</b> <b>M12 Plug connector</b> <b>SK TIE4-M12-CAO</b>	<b>BUS technology box</b> <b>SK TU4-CAO (-M12) / (-C)</b> <b>BUS connection unit</b> <b>SK TI4-TU-BUS (-C)</b>	<b>BUS customer interface</b> <b>SK CU4-CAO</b>																																									
	<table border="1"> <thead> <tr> <th>Pin</th> <th>Colour</th> <th>Signal</th> <th>Contact</th> <th>Designation</th> <th>Contact</th> <th>Designation</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>white</td> <td>Shield</td> <td>9</td> <td>SHLD</td> <td>90</td> <td>SHLD</td> </tr> <tr> <td>2</td> <td>Brown</td> <td>+24 V</td> <td>1</td> <td>24V-B CAO</td> <td>45</td> <td>24V bus</td> </tr> <tr> <td>3</td> <td>Blue</td> <td>GND</td> <td>7</td> <td>GND B CAO</td> <td>46</td> <td>GND Bus</td> </tr> <tr> <td>4</td> <td>Black</td> <td>CAN_H</td> <td>3</td> <td>CAO+ OUT</td> <td>75 (incoming)</td> <td>CANopen+</td> </tr> <tr> <td>5</td> <td>grey</td> <td>CAN_L</td> <td>5</td> <td>CAO- OUT</td> <td>76 (incoming)</td> <td>CANopen-</td> </tr> </tbody> </table>	Pin	Colour	Signal	Contact	Designation	Contact	Designation	1	white	Shield	9	SHLD	90	SHLD	2	Brown	+24 V	1	24V-B CAO	45	24V bus	3	Blue	GND	7	GND B CAO	46	GND Bus	4	Black	CAN_H	3	CAO+ OUT	75 (incoming)	CANopen+	5	grey	CAN_L	5	CAO- OUT	76 (incoming)	CANopen-	
Pin	Colour	Signal	Contact	Designation	Contact	Designation																																						
1	white	Shield	9	SHLD	90	SHLD																																						
2	Brown	+24 V	1	24V-B CAO	45	24V bus																																						
3	Blue	GND	7	GND B CAO	46	GND Bus																																						
4	Black	CAN_H	3	CAO+ OUT	75 (incoming)	CANopen+																																						
5	grey	CAN_L	5	CAO- OUT	76 (incoming)	CANopen-																																						

Optional accessories

**i** Information

**M12 / M20 screw openings**



Conductive connection extensions made from brass SK TIE4-M12-M16 from M12 to M16 or connection reductions SK TIE4-M20-M16 from M20 to M16 are optionally available for installing the M12 connection extensions in an M12 or M20 screw opening. For more information, see further documentation.

Further documentation ([www.nord.com](http://www.nord.com))

Document	Designation
<a href="#">BU 0180</a>	SK 180E, SK 190E frequency inverter manual
<a href="#">BU 0200</a>	Frequency inverter manual SK 2xxE
<a href="#">BU 0260</a>	CANopen for SK 200E manual
<a href="#">BU 0280</a>	DEVICENET for SK 200E manual
<a href="#">TI 275280000</a>	Bus connection unit SK TI4-TU-BUS
<a href="#">TI 275280500</a>	Bus connection unit SK TI4-TU-BUS-C
<a href="#">TI 275274510</a>	Connection extension SK TIE4-M12-M16
<a href="#">TI 275274511</a>	Connection reduction SK TIE4-M20-M16
<b>TI 275271001</b>	CANopen bus interface SK CU4-CAO
<b>TI 275281101</b>	CANopen bus interface SK TU4-CAO

Document	Designation
<b>TI 275281151</b>	CANopen bus interface SK TU4-CAO-C
<b>TI 275281201</b>	CANopen bus interface SK TU4-CAO-M12
<b>TI 275281251</b>	CANopen bus interface SK TU4-CAO-M12-C
<b>TI 275271002</b>	DeviceNet bus interface SK CU4-DEV
<b>TI 275281102</b>	DeviceNet bus interface SK TU4-DEV
<b>TI 275281152</b>	DeviceNet bus interface SK TU4-DEV-C
<b>TI 275281202</b>	DeviceNet bus interface SK TU4-DEV-M12
<b>TI 275281252</b>	<b>DeviceNet bus interface SK TU4-DEV-M12-C</b>
<b>TI 275274515</b>	Connection extension SK TIE4-M12-CAO-OUT