


GETRIEBEBAU NORD

Member of the NORD DRIVESYSTEMS Group

Getriebebau NORD GmbH & Co. KG

Getriebebau-Nord-Straße 1 • 22941 Bargteheide, Germany • www.nord.com



SK CE-HANQ2-K-BRE-OE-2_0M

Part number: 275 274 881

Cable for connection of an external braking resistor to a
NORDAC LINK SK 2xxE-FDS



Only qualified electricians are allowed to install and commission the module. An electrician is a person who, because of their technical training and experience, has sufficient knowledge with regard to

- switching on, switching off, isolating, earthing and marking power circuits and devices,
- proper maintenance and use of protective devices in accordance with defined safety standards.

DANGER!

Danger of electric shock

The frequency inverter continues to carry hazardous voltages for up to 5 minutes after it was switched off.

- Work must not be carried out unless the device has been disconnected from the voltage and at least 5 minutes have elapsed since the mains was switched off!

CAUTION

Danger of burns

The module and all other metal components can heat up to temperatures above 70 °C.

Sufficient cooling time must be allowed for when working on the components in order to avoid injuries (local burns) to parts of the body coming into contact with the components.

In order to avoid damage to neighbouring objects, sufficient clearance must be maintained during installation.

NOTICE

Validity of this document

This document is only valid in combination with the operating instructions for the relevant frequency inverter. Safe commissioning of this module and the frequency inverter depends on the availability of this information.

Scope of delivery

1 x	Connection cable 2.0 m incl. HAN Q2 plug connector
-----	--



Technical Information / Datasheet	SK CE-HANQ2-K-BRE-OE-2_0M			
accessories	TI 275274881	1.0	3018	en

Field of use

Shielded connection cable for plug connection of an external braking resistor directly to a *NORDAC LINK* SK 2xxE-FDS with a HAN Q2 plug connector. For Size 1, connection is made to option slot X2 of the SK 2xxE-FDS. For Size 2, in addition to option slot X2, X4 is also available for connection of the braking resistor.



Technical Data

General

Tightening torque		
Cable gland M20	Nm	1.5 – 2.0
Weight	kg	0.36
Testing voltage	V	1000

Certifications	UL, CSA, CE, RoHS
Protection class	IP67
Fastening	
Stirrup clamp	Engage

Plug connector type	HAN Q 2/0 (Pin, M)
Number of contacts	2 +PE
Cable cross-section	2.5 mm ²
Rated current	40 A
Rated voltage	830 V
Housing	Plastic, black
Contact insert	Pin insert (M)
Version	straight

Connection cables	
Cable gland	M20 x 1 Plastic, black
Cable connection	Open end of cable
Type	Shielded

Dimensions

Connection cable [mm]		
Length	L	2120
Lead black / black	L	30
Lead green / grey / white	L	40
Separate lead	L	10
Housing	W x H x D	35.1 / 26.5 / 60



Connections

HAN Q 2/0 connections	Wire colour	Cable labelling	Cable number
1	Black	B- (braking resistor)	1
2	Black	B+ (braking resistor)	2
2	Green Yellow	PE	PE

Further documentation and software: www.nord.com

Document	Name
BU_0250	Manual for frequency inverters SK 250E-FDS – SK 280E-FDS as field distributors

Part No.	Name	Option / Component
TI 278281070	SK BRW5-1-300-225	External 300 Ω braking resistor Size 1 for wall mounting
TI 278281071	SK BRW5-2-150-450	External 150 Ω braking resistor Size 2 for wall mounting