

Drive Solutions for Drag/Chain Conveyors





Reliable Under All Conditions

Drag conveyor drive solutions from NORD provide reliable operation for moving grain and other bulk materials horizontally or on inclines. They are ideal for outdoor installations and can handle many application environments. NORD drag conveyor drives also have significant advantages with regard to safety, environmental protection, and efficiency.



NORD products are suitable for all drag conveyor applications that require multiple loading or discharge points such as transferring and removing products from bulk storage bins.

Flat Bottom Drag Conveyors

- ▶ Ideal for handling free flowing bulk materials
- Designed and engineered to provide long life and durability with minimum maintenance
- Gentle, fast movement of the transferred material via a fully enclosed dust-tight conveyor

Round Bottom Drag Conveyors

- Designed with an elevated head and tail section
- ▶ Helps to reduce noise, vibration, and chordal action

L-Path or S-Path Drag Conveyors

- ▶ A single (L-Path) or multiple (S-Path) direction change adapts the conveyor to the plant design
- Expensive changes to the plant layout can be avoided
- ▶ Can also discharge from a vertical position

Mill Duty Drag Conveyors

 Ideal for handling heavier, abrasive products such as aggregate, limestone, and sand

Drive Solutions for Drag/Chain Conveyors



Reliable and Robust Gear Units for All Types of Drag Conveyors

UNICASE™ Helical Bevel Gear Units (Catalog G1000)



- ✓ Foot, flange, or face mounted
- ✓ Hollow or solid shaft
- ✓ Long life, low maintenance
- ✓ Cast-iron UNICASE housing

Sizes: 11

Power: 0.16 – 200 hp Torque: 1,593 – 442,537 lb-in Speed ratio: 8.04:1 – 13,432.68:1

UNICASE™ Helical Inline Gear Units (Catalog G1000)



- ✓ Foot, flange, or face mounted
- ✓ Optimum sealing
- ✓ Long life, low maintenance
- ✓ Cast-iron UNICASE housing

Sizes: 11

Power: 0.16 – 200 hp Torque: 89 – 230,119 lb-in Speed ratio: 2.76:1 – 14,340.31:1

MAXXDRIVE® Industrial Gear Units (Catalog G1050)



- ✓ Parallel axis and right-angled gear units
- ✓ High radial load capacity
- ✓ Long life, low-maintenance
- ✓ UNICASE housings
- ✓ Hollow or solid shaft
- ✓ Foot or flanged motor (B3 / B5 / C-face)
- ✓ Backstop

Sizes: 11

Power: 2.5 – 8,075 hp

Torque: 132,800 – 2,495,900 lb-in Ratio: 5.54:1 – 30,000:1

UNICASE™ Parallel Shaft Gear Units (Catalog G1000)



- ✓ Foot, flange, or face mounted
- ✓ Hollow or solid shaft
- ✓ Compact design
- Cast-iron or aluminum UNICASE housing

Sizes: 15

Power: 0.16 – 200 hp Torque: 974 – 680,200 lb-in Speed ratio: 4.03:1 – 15,685.03:1





Driven by Energy Efficient Motors for All Types of Environment

Motors (Catalog M7000): Standard Motors with Recommended Options:



RD/RDD	Rain Drip Canopy/ Double Fan Drip Cover
PTC / KTY / PT100	Resistance thermometers
IE2 motors	for VFD driven motors
IE2 motors	for direct online driven motors

Protected against water and dust



Hazardous Area ATEX

All gear units are also available as: Dust explosion protected drive solution Gas explosion protected drive solution

Energy Efficient

NORD drive solutions are environmentally friendly and help reduce operating costs and minimize CO₂ emissions.

- ▶ High efficiency helical and bevel gear units achieve optimum power transmission performance
- ▶ NORD motors comply with international energy efficiency classes up to IE5+









▶ NORD variable frequency drives have energy saving functions to effectively reduce energy consumption

Drive Solutions for Drag/Chain Conveyors




Available Options and Solutions:

- Direct mounting, elastic coupling, or belt-driven input shaft to transfer torque
- ▶ Backstop to avoid return of material in case of power failure
- Special seals to cope with harsh environments
- Hollow shaft or solid shaft depending on drag conveyor connection
- Fixing element for attaching the hollow shaft
- > Shrink disc for attaching the hollow shaft
- ▶ Cover (IP66) to provide additional protection

- Stainless steel shafts for corrosion protection
- ATEX for explosive atmospheres
- NORD soft starter for smooth start and stop, as well as reverse operation function
- NORD variable frequency drives for speed, torque, and process control

Complete Drive Solutions From a Single Source



US

Central Region Corporate Headquarters 800 NORD Drive Waunakee, WI 53597 Tel. 888.314.6673 info.us@nord.com www.nord.com East Region 300E Forsyth Hall Dr. Charlotte, NC 28273 Tel. 888.314.6673 info.us@nord.com West Region 1180 Railroad St. Corona, CA 92882 Tel. 888.314.6673 info.us@nord.com South Region 350 Cypress Hill Dr, Suite 400 McKinney, TX 75071 Tel. 888.314.6673 info.us@nord.com

CA

NORD Gear Limited Brampton, ON 41 West Drive Brampton, ON L6T4A1 Tel. 800.668.4378 info.ca@nord.com

MX

NORD DRIVE SYSTEMS SA DE CV Queretaro, Mexico Av. Industria Textil B.6 Parque Industrial PYME, Huimilpan QRO - Mexico 76950 Tel. 52 442 688 7110 info.mx@nord.com