
Intelligent Drivesystems



FLEXBLOC™ & MINICASE® WORM DRIVES Speed Reducer / Gear Motors



FLEXBLOC™ & MINICASE® **Speed Reducers**



FLEXBLOC™ and MINICASE® Worm Gears

NORD modular worm gear products cover 5 industry standard center distances from 31 mm-75 mm (1.2 in-3.0 in) and range in torque capacity up to 3,779 lb-in. This product offering comes in a variety of standard, single worm, and compound worm ratios ranging from 5:1 to 10,000:1. The product family consists of the FLEXBLOC™ (SI Series) worm with universal gear housing and the MINICASE® (SMI Series) worm characterized by its smooth outer surface design and its separate footed and flanged gear housing. Exceptional modularity is guaranteed by offering a unified set of factory-stocked and easy-to-assemble accessory kits. This flexibility allows for a variety of input and output mounting options along with a large variety of output shaft options. The FLEXBLOC™ and MINICASE® worm gear products share many innovative design features.






FLEXBLOC™ Key Features:

- Universal foot and flange-mount housings Keyed hollow-bore units with solid shaft kits
- Adaptable to any mounting position

- Easy to assemble accessories NEMA, IEC, or solid shaft input as standard Accommodates stocked C-Face motors or brakemotors





MINICASE® Key Features:

- Factory-assembled from stocked parts
- Separate smooth-bodied foot &
- flange-mount housings Keyed hollow-bore or one-piece
- Specific bores accommodate plug-in shafts
- Easy to assemble accessories
- Supplied as an integral motor or brakemotor (C-Face motorized options possible)



Product Features

Dual Pinion Shaft Bearings

Two bearing supports maintain accurate gear and shaft alignment, isolate and protect motor bearings, and provide smooth/quite operation.

Input Configuration

NEMA, IEC and free input shaft designs are readily available. Integral motor mounting is optional. Adaptation to servo motors is possible.

Motor Coupling

Guarantees accurate motor shaft alignment, minimizes fretting and provides a low backlash / high strength connection.

Worm Pinion Gear

Surfaced hardened alloy steel gears with an optimized tooth form maximize gear contact and provide long service life.

Alluminum Alloy Housing


Light weight, high strength, optimal heat dissipation and natural corrosion resistance. Flange or torque-arm mount options available.

Worm Gear

Fine-grained bronze alloy minimizes wear providing maximum strength and durability.

Output Shaft

Hollow bore and singlesided or double-sided shafted models are also available.






Oversized bearings provide high radial and axial load capacities and long service life.

Oil Seals

Double-lip oil seals provide extra sealing and protection against the elements.




- Easy to assemble and disassemble.
- Eliminates fretting corrosion common to quill-mount inputs.
- Maintains shaft alignment and provides vibration-free torque transfer.
- Protects and isolates motor shaft and reducer shaft bearings.
- Provides a stiff, high-strength, near-zero backlash connection.
- Reduces the chance of bearing, shaft and key failures.





Innovative Design Features





UNICASE® One Piece Housing

NORD heavy-duty, one-piece housings are precisely machined to exacting standards. Internal reinforcements further increase strength and rigidity. All bearings and seal seats are contained within the casting, eliminating splits or bolt-on carriers that can weaken the housing and allow oil leakage. Bores and mounting faces are machined in one step, producing extremely precise tolerances — thus ensuring accurate positioning of gear teeth, bearings and seals, and longer life for all components.

- Increased torsional strength and rigidity.
- Eliminates housing splits and bolt-on carriers.
- Leak-free housing design.
- Versatile mounting options and accessory kits.

Modular Construction

- Easy-to-configure input and output accessories.
- Integral motor or motorized c-face units.
- NEMA, IEC or solid shaft input options.
- Footed, flanged or shaft-mount.
- 10:1 helical pre-stage & compound assemblies.
- Keyed hollow bore, solid shaft, and bushing-kit options.





Factory Oil Filled

NORD factory-filled gear units allow for easy commissioning of the gear unit and prevent damage caused by dry start-ups. Each unit is filled with a quality gear lubricant that is recognized by the industry.

- Maintence free / lubricated-for-life.
- High-quality long-life synthetic lubricant.
- USDA H1 lubrication readily available.
- Optional venting capabilities.



FLEXBLOC™& MINICASE® Flexible Solutions & Bolt-On Modules



NEMA C-FACE COUPLING ADAPTER

For attaching standard motors

Kit contains:

- Adapter flange
- Coupling
- Nuts and bolts

2ND REDUCTION

Helical 10:1 gear set Fits all size gearboxes Lifetime synthetic lubricant Sealed unit

Kit contains:

- Pre-assembled unit
- Bolts

SOLID INPUT SHAFT

Fits all size gearboxes Lifetime lubricant Sealed unit

Kit contains:

- Pre-assembled unit

DOUBLE WORM ADAPTER

Mounts the SK1SI/SMI31 to the input of the larger SK1SI/SMI40 - SK1SI/SMI75 to produce a high reduction double worm gear unit

Kit contains:

- Adapter flange
- Coupling
- Shaft
- Keys
- Bolts


NORD C-FACE MOTORS & BRAKEMOTORS

3 phase, 230/460, 60 Hertz 3 phase, 575V, 60 Hertz


Options:

- Power off brake
- Numerous brake options
- Thermistor temperature sensors
- Thermostat temperature sensors
- Blower fan

- Encoders
- Space heater
- Canopy drip covers
- Encapsulated windings
- End bell drain holes







SOLID OUTPUT SHAFT

Inch dimensions with standard keys Plug into standard hollow shaft Install on either side

Kit contains: • Shaft

Options:

- Double solid shaft
- Keys
- External snap ring

B5 OUTPUT FLANGE

Multiple flanges available for each size gearbox. Flange pilots are centered in seal bore.

Kit contains:

- Die cast flange
- Bolts

SHAFT PROTECTION COVER

Seals shaft end Safety protection from rotating shafts.

Kit contains:

- Cover
- Bolts

FOOT PLATE

Mounts to the bottom of the FLEXBLOC™ to provide drop-in compatibility with many worm gear reducers.

Kit contains:

- Foot plate
- Bolts

TORQUE REACTION ARM

For shaft mounting

Rubber shock absorber installed in attachment end.

Kit contains:

- Torque arm
- Bolts

SHAFT BUSHING

Hollow shaft bushing for increased bore flexibility.

Kit contains:

- Bushings with set screw
- Key

FIXING KIT

Optional mounting device that engages the customer solid shaft tap and draws the end of the shaft into contact with the hollow bore snap ring.

Kit contains:

- Carbon Steel retaining washer and bolt
- Spring loaded steel snap ring
- Plastic cover





Gearbox Ratings



- 5:1 100:1 single worm ratios.
- Up to 1000:1 with a 10:1 helical pre-stage option.
- Compound Unit ratios up to 10,000:1

Туре	Ratio	Output RPM	Torque [lb-in]	Max Input HP
SK 1SI 31	5	350	204	1.30
3K 13131	7.5	233	239	1.06
	10	175	230	0.80
SK 1SMI 31	12.5	140	212	0.61
	15	117	257	0.66
	20	88	239	0.49
	25	70	221	0.38
	30	58	266	0.44
	40	43	248	0.34
	50	35	230	0.27
	60	29	212	0.23
	80	22	195	0.18
	100	18	186	0.17

Туре	Ratio	Output RPM	Torque [lb-in]	Max Input HP
SK 1SI 40	5	350	336	2.10
3K 131 40	7.5	233	389	1.69
	10	175	372	1.24
SK 1SMI 40	12.5	140	363	1.00
	15	117	434	1.06
	20	88	398	0.77
	25	70	372	0.60
	30	58	442	0.67
	40	43	407	0.51
	50	35	381	0.41
	60	29	354	0.34
	80	22	327	0.27
	100	18	301	0.23
SK 1SI 40/H10	50	35	549	0.38
SK 1SMI 40/H10		th	ru	
3K 13MI 4U/ H IU	1000	1.8	487	0.06
SK 1SI 40/31	150	12	655	0.30
SK 1SMI 40/31		th	ru	
3K 13WI 4U/31	3000	0.6	876	0.06

Туре	Ratio	Output RPM	Torque [lb-in]	Max Input HP
SK 1SI 50	5	350	584	3.56
	7.5	233	690	2.90
SK 1SMI 50	10	175	664	2.14
	12.5	140	637	1.69
	15	117	770	1.79
	20	88	717	1.30
	25	70	673	1.01
	30	58	796	1.11
	40	43	<i>7</i> 35	0.83
	50	35	681	0.65
	60	29	646	0.55
	80	22	593	0.43
	100	18	549	0.36
SK 1SI 50/H10	50	35	742	0.50
		th	ru	
SK 1SMI 50/H10	1000	1.8	894	0.09
SK 1SI 50/31	150	12	11 <i>77</i>	0.49
SK 1SMI 50/31		th	ru	
3K 13/VII 3U/ 3 I	3000	0.6	1575	0.11

Туре	Ratio	Output RPM	Torque [lb-in]	Max Input HP
SK 1SI 63	5	350	1044	6.30
	7.5	233	1230	5.05
SK 1SMI 63	10	1 <i>75</i>	1186	3.74
	12.5	140	1142	2.91
	15	11 <i>7</i>	1372	3.07
	20	88	1274	2.22
	25	70	1195	1.72
	30	58	1416	1.86
	40	43	1301	1.38
	50	35	1212	1.09
	60	29	1150	0.90
	80	22	1044	0.69
	100	18	974	0.57
SK 1SI 63/H10	50	35	<i>75</i> 1	0.50
· .		th	ru	
SK 1SMI 63/H10	1000	1.8	1584	0.16
SK 1SI 63/31	150	12	2097	0.83
·		th	ru	
SK 1SMI 63/31	3000	0.6	2797	0.20

Туре	Ratio	Output RPM	Torque [lb-in]	Max Input HP
SK 1SI 75	5	350	1 <i>7</i> 35	10.36
3K 131 /3	7.5	233	2071	8.41
	10	175	2009	6.2
SK 1SMI 75	12.5	140	1912	4.77
	15	11 <i>7</i>	2336	5.1
	20	88	2168	3.65
	25	70	2036	2.79
	30	58	1929	2.25
	40	43	2212	2.21
	50	35	2062	1.71
	60	29	1956	1.41
	80	22	1 <i>77</i> 9	1.05
	100	18	1655	0.88
	150	12	2832	0.96
SK 1SI 75/40		th	ru	
	3000	0.60	3779	0.19

Motor **Ratings**

Motor Specifications







Inverter duty • TEFC Synchronous speed 1800rpm @ 60Hz • 4-pole • Three-phase 1.15 Service Factor • Continuous Duty • 40°C Ambient up to 3300ft Elevation • Class B temperature rise Class F insulation



230/460V or 200-208V or 575V – 60Hz




Po	wer	Speed	Motor Type (Frame)		
[hp]	[kW]	[rpm]	Integral	NEMA C-Face	
0.16	0.12	1700	63 S/4	63 S/4-56C	
0.25	0.18	1680	63 L/4	63 L/4-56C	
0.33	0.25	1710	71 S/4	71 S/4-56C	
0.5	0.37	1720	71 L/4	71 L/4-56C	
0.75	0.55	1710	80 S/4	80 S/4-56C	
1	0.75	1650	80 L/4	80 L/4-56C	

230/460V+ or 575V - 60Hz Energy Efficient (EPAct)



112 MP/4-184TC

Pov	ver	Speed	Motor Type (Frame)				
[hp]	[kW]	[rpm]	Integral	NEMA C-Face			
1	0.75	1750	80 LH/4	80 LH/4-56C			
1	0.75	1750	80 LH/4	80 LH/4-143TC			
1.5	1.1	1740	90 SH/4	90 SH/4-145TC			
2	1.5	1745	90 LH/4	90 LH/4-145TC			
3	2.2	1765	*	100 LH/4-182TC			
5	3.7	1770	*	112 MH/4-184TC			



^{+ 208-230/460}V Rating Possible






230/460V+ or 575V – 60Hz | **Premium Efficient** (EISA) (pe) **Power Speed Motor Type (Frame)** [hp] [kW] **NEMA C-Face** [rpm] Integral 1750 0.75 80 LP/4 80 LP/4-56C 0.75 1750 80 LP/4 80 LP/4-143TC 1.5 1.1 1740 90 SP/4 90 SP/4-145TC 2 1.5 1745 90 LP/4 90 LP/4-145TC 3 2.2 1765 100 LP/4-182TC

1770

3.7

5






^{*} Consider a gear unit with NEMA C-face input

^{+ 208-230/460}V Rating Possible

FLEXBLOC™ Worm Dimensions



DIMENSIONS

	Α	В	D	E	F	0	QA	U	UH
SK 1SI 31	3.15	2.48	1.57	2.13	1.73	3.82	3.82	0.625	0.625
SK 1SI 40	3.94	3.07	1.97	2.76	2.36	4.78	4.69	0.750	1.000
SK 1SI 50	4.72	3.62	2.36	3.15	2.76	5.67	5.16	1.000	1.125
SK 1SI 63	5.67	4.41	2.83	3.94	3.35	6.85	6.22	1.125	1.4375
SK 1SI 75	6.77	5.12	3.39	4.72	3.54	8.08	7.87	1.375	1.9375

Metric Shaft available

NEMA C-FACE DIMENSIONS


	48	48C		56C		ОТС	180TC		
	Available	СС	Available	СС	Available	СС	Available	CC	
SK 1SI 31	Х	1.50	Х	1.89	-	-	-	-	
SK 1SI 40	-	-	X	1.46	X	1.93	-	-	
SK 1SI 50	-	-	Х	1.46	Х	1.93	-	-	
SK 1SI 63	-	-	Х	1.46	Х	1.93	Х	3.06	
SK 1SI 75	-	-	Х	1.61	X	1.61	X	2.16	

NEMA C-FACE GEARMOTOR DIMENSIONS

	56C-(63S/L	56C-71S/L		56C-80S/L-LH-LP		140TC-8	140TC-80L-LH-LP		140TC-90LH-LP		180TC-100LH-LP		180TC-112MH-MP	
	L	L BR	L	L BR	L	L BR	L	L BR	L	L BR	L	L BR	L	L BR	
SK 1SI 31	7.57	9.78	8.44	10.72	9.46	11.98	9.46	11.98	-	-	-	-	-	-	
SK 1SI 40	7.57	9.78	8.44	10.72	9.46	11.98	9.46	11.98	11.00	13.95	-	-	-	-	
SK 1SI 50	7.57	9.78	8.44	10.72	9.46	11.98	9.46	11.98	11.00	13.95	-	-	-	-	
SK 1SI 63	7.57	9.78	8.44	10.72	9.46	11.98	9.46	11.98	11.00	13.95	11.97	15.57	-	-	
SK 1SI 75	-	-	8.44	10.72	9.46	11.98	9.46	11.98	11.00	13.95	11.97	15.57	13.56	17.26	



MINICASE® Worm Dimensions



GEARBOX & SHAFT DIMENSIONS

	Α	В	D	Е	F	0	QA	U	UH
SK 1SMI 31	3.27	3.54	1.57	2.56	2.95	3.54	3.82	0.500	0.625
SK 1SMI 40	3.78	4.72	2.09	3.15	3.94	4.53	4.69	0.750	1.000
SK 1SMI 50	4.72	4.72	2.48	3.15	3.94	5.24	5.16	1.000	1.125
SK 1SMI 63	5.67	5.31	2.95	3.94	4.33	6.34	6.18	1.250	1.4375
SK 1SMI 75	6.77	6.69	3.54	5.12	5.51	7.94	7.87	1.375	1.9375

NEMA C-FACE DIMENSIONS

Metric Shaft available

	48C		50	56C		ОТС	180TC		
	Available	СС	Available	СС	Available	СС	Available	СС	
SK 1SMI 31	Х	1.50	Х	1.89	-	-	-	-	
SK 1SMI 40	-	-	Х	1.46	X	1.93	-	-	
SK 1SMI 50	-	-	Х	1.46	Х	1.93	-	-	
SK 1SMI 63	-	-	Х	1.46	X	1.93	X	3.06	
SK 1SMI 75	-	-	Х	1.61	X	1.61	Х	2.16	

INTEGRAL GEARMOTOR DIMENSIONS

	63S/L		71S/L		80S/L/SH/LH/SP/LP		90SH/LH/SP/LP		100LH/LP		112MH/MP	
	L	L BR	L	L BR	L	L BR	L	L BR	L	L BR	L	L BR
SK 1SMID 31	7.57	9.78	8.44	10.72	-	-	-	-	-	-	-	-
SK 1SMID 40	7.59	9.79	8.44	10.72	9.31	11.83	-	-	-	-	-	-
SK 1SMID 50	-	-	8.44	10.72	9.31	11.83	10.84	13.80	-	-	-	-
SK 1SMID 63	-	-	-	-	9.31	11.83	10.84	13.80	-	-	-	-

NEMA C-FACE GEARMOTOR DIMENSIONS

	56C-63S/L		56C-71S/L		56C-80S/L-LH-LP		140TC-80L-LH-LP		140TC-90LH-LP		180TC-100LH-LP		180TC-112MH-MP	
	L	L BR	L	L BR	L	L BR	L	L BR	L	L BR	L	L BR	L	L BR
SK 1SMI 31	7.57	9.78	8.44	10.72	9.46	11.98	9.46	11.98	-	-	-	-	-	-
SK 1SMI 40	7.57	9.78	8.44	10.72	9.46	11.98	9.46	11.98	11.00	13.95	-	-	-	-
SK 1SMI 50	7.57	9.78	8.44	10.72	9.46	11.98	9.46	11.98	11.00	13.95	-	-	-	-
SK 1SMI 63	7.57	9.78	8.44	10.72	9.46	11.98	9.46	11.98	11.00	13.95	11.97	15.57	-	-
SK 1SMI 75	-	-	8.44	10.72	9.46	11.98	9.46	11.98	11.00	13.95	11.97	15.57	13.56	1 <i>7</i> .26

Product Overview

UNICASE™ SPEED REDUCERS



HELICAL IN-LINE

- Foot or Flange Mount
- Torque up to 205,000 lb-in
- Gear ratios 1.82:1 to over 300,000:1



NORDBLOC®.1 HELICAL IN-LINE

- Foot or Flange Mount
- Torque up to 26,550 lb-in
- Gear ratios 1.88:1 to over 370:1



PARALLEL HELICAL CLINCHER™

- Shaft, Flange or Foot Mount
- Torque up to 797,000 lb-in
- Gear ratios 4.26:1 to over 300,000:1



SCP SCREW CONVEYOR PACKAGE

- Shaft, or Flange Mount
- Torque up to 53,100 lb-in
- Gear ratios 4.32:1 to over 1500:1



RIGHT ANGLE HELICAL-BEVEL 2-STAGE

- Foot, Flange or Shaft Mount
- Torque up to 5,840 lb-in
- Gear ratios 4.1:1 to 72:1



RIGHT ANGLE HELICAL-BEVEL

- Foot, Flange or Shaft Mount
- Torque up to 283,000 lb-in
- Gear ratios 8.04:1 to over 300,000:1



RIGHT ANGLE HELICAL-WORM

- Foot, Flange or Shaft Mount
- Torque up to 27,585 lb-in
- Gear ratios 4.40:1 to over 300,000:1

HIGH PERFORMANCE MOTORS & BRAKEMOTORS



INVERTER/VECTOR DUTY

- Standard or Energy Efficient
- Integral, NEMA or Metric IEC
- 1/6 to 250 hp

UNICASE™ SPEED REDUCERS



MINICASE™ RIGHT ANGLE WORM

- Foot, Flange or Shaft Mount
- Torque up to 3,540 lb-in
- Gear ratios 5:1 to 500:1



FLEXBLOC[™] WORM

- Modular bolt-on options
- Torque up to 4,683 lb-in
- Gear ratios 5:1 to 3,000:1



MAXXDRIVE™ LARGE INDUSTRIAL **GEAR UNITS PARALLEL HELICAL**

- Modular bolt-on options
- Torque up to 2,027,000 lb-in
- Gear ratios 5:1 to 1,600:1



MAXXDRIVE™ LARGE INDUSTRIAL **GEAR UNITS HELICAL-BEVEL**

- Modular bolt-on options
- Torque up to 2,027,000 lb-in
- Gear ratios 5:1 to 1,600:1

NORDAC AC VECTOR DRIVES



SK200E FAMILY

- Decentralized, high performance
- 380-480V, 3-phase to 10 hp
- 200-240V, 3-phase to 5 hp
- 200-240V, 1-phase to 1.5 hp
- 100-120V, 1-phase to 1 hp



SK500E FAMILY

- Compact, high performance
- 380-480V, 3-phase, to 50hp
- 200-240V, 3-phase, to 15hp
- 200-240V, 1-phase, to 3hp
- 110-120V, 1-phase, to 1.5hp

NORD Gear Corporation MEMBER OF THE NORD DRIVESYSTEMS GROUP

National Customer Service Toll-Free: 888.314.6673 info.us@nord.com

NORD Gear Limited
MEMBER OF THE NORD DRIVESYSTEMS GROUP
Toll-Free in Canada: 800.668.4378 info.ca@nord.com

CANADA

Brampton, ON (Toronto) Phone: 905.796.3606

DRIVESYSTEMS

www.nord.com

Corona, CA (Los Angeles) Phone: 608.849.0190

MIDWEST

Waunakee, WI (Madison) Phone: 608.849.7300

Charlotte, NC

Phone: 608.849.0140