

GETRIEBEBAU NORD

Member of the NORD DRIVESYSTEMS Group



Getriebebau NORD GmbH & Co. KG

Getriebebau-Nord-Straße 1 • 22941 Bargteheide, Germany • www.nord.com


SK CE-HQ42-K-LE-OE-xxM

Cable Mains

with 24V DC voltage supply

Scope of supply

1 x	Power plug, 6-poles + PE										
1 x	Cable set with 6 single conductors										
<table border="1"> <thead> <tr> <th>Part number</th> <th>Cable length</th> </tr> </thead> <tbody> <tr> <td>275 274 845</td> <td>1.5 m</td> </tr> <tr> <td>275 274 846</td> <td>3 m</td> </tr> <tr> <td>275 274 847</td> <td>5 m</td> </tr> <tr> <td>275 274 848</td> <td>10 m</td> </tr> </tbody> </table>		Part number	Cable length	275 274 845	1.5 m	275 274 846	3 m	275 274 847	5 m	275 274 848	10 m
Part number	Cable length										
275 274 845	1.5 m										
275 274 846	3 m										
275 274 847	5 m										
275 274 848	10 m										
The open wires are not prepared for connection.											



It only is allowed for qualified electricians to install and commission the module. An electrician is a person who, because of their technical training and experience, has sufficient knowledge relating to

- switching on, switching off, isolating, earthing and marking power circuits and devices,
- proper maintenance and use of protective devices in accordance with defined safety standards.



DANGER!

Danger of electric shock

The frequency inverter continues to carry hazardous voltages for up to 5 minutes after it was switched off.

- Work must not be carried out unless the device has been disconnected from the voltage and at least 5 minutes have elapsed since the mains was switched off!

Field of use

This mains incoming cable is useable to connect the electronic device via plug.

The power plug HAN Q4/2 (4x power contacts + PE and 2 signal contacts) will be used for the mains incoming and the control voltage of the electronic device.



Electronic connection

Mains connection incl. 24V DC

Technical Information / Datasheet	SK CE-HQ42-K-LE-OE-xxM			
Specification of connection cable	TI_275274845-848	1.0	3419	en

i Information
Fixed laying system for the cable!


This cable is only useable for fixed (not moved) installation. All values for the fixed laying system are noted on this data sheet. Other laying systems are not allowed with this cable type.

Technical Data

Specification	Plug
Number of contacts	4/2 + PE
Type of contacts	Female (F)
Rated current I _N	16 A [power]
Rated voltage	400 V (EU), [power]
Rated current I _N	10 A [signal]
Rated voltage	250 V (EU), [signal]
Plug housing:	Plastic
Limit temperature	-40°... +80 °C
Pollution degree	3

Specification	Cable
Standard	VDE 0285, 0295
Designation	4G4 + (2x1,5)
Bending radius	4x cable diameter
Outside diameter	approx. 12,8 mm
Insulation material	PVC
Conductor material	Cu, Blanc
Conductor type	Finely stranded
Laying system	Fixed (not moved)
Open wires	Not dismantled

PIN assignment

Potential	PIN assignment Electronics	Cable color: designation acc. to DIN VDE 0293	Open wires Mains connection
L1	1	Black: 1 / L1	Single wire ø 4 mm.
L2	2	Black: 2 / L2	Single wire ø 4 mm.
L3	3	Black: 3 / L3	Single wire ø 4 mm.
	GNYE	Green	Single wire ø 4 mm.
		Yellow	
+24V DC	11	Black: 4	Single wire ø 1.5 mm.
GND	12	White: 5	Single wire ø 1.5 mm.