

# GETRIEBEBAU NORD

Member of the NORD DRIVESYSTEMS Group



Getriebebau NORD GmbH & Co. KG

Getriebebau-Nord-Straße 1 • 22941 Bargteheide, Germany • www.nord.com

## SK CE-HQ4-K-LA-HQ4-xxM

### Cable Daisy-Chain

#### Scope of supply

2 x	Power plug, 6-poles + PE
1 x	Cable set with 4 single conductors

Part number	Cable length
275 274 850	1.5 m
275 274 851	3 m
275 274 852	5 m
275 274 853	10 m
275 274 885	15 m
275 274 886	20 m
275 274 887	30 m
275 274 888	40 m
275 274 889	50 m

This cable has a plug at both ends.



It only is allowed for qualified electricians to install and commission the module. An electrician is a person who, because of their technical training and experience, has sufficient knowledge relating to

- switching on, switching off, isolating, earthing and marking power circuits and devices,
- proper maintenance and use of protective devices in accordance with defined safety standards.

### DANGER!

#### Danger of electric shock

The frequency inverter continues to carry hazardous voltages for up to 5 minutes after it was switched off.


- Work must not be carried out unless the device has been disconnected from the voltage and at least 5 minutes have elapsed since the mains was switched off!

#### Field of use

The daisy chain cable is useable to supply mains voltage supply between two electronic devices.

The power plug HAN Q4/2 (4x power contacts + PE) will be used for the mains incoming voltage of the electronic device.

Technical Information / Datasheet	SK CE-HQ4-K-LA-HQ4-xxM			
Specification of connection cable	TI_275274850-853	1.0	2019	en



Output: Mains connection

Input: Mains connection

**i Information**

**Fixed laying system for the cable!**



This cable is only useable for fixed (not moved) installation. All values for the fixed laying system are noted on this data sheet. Other laying systems are not allowed with this cable type.

**Technical Data**

Specification	Plugs
Number of contacts	4 + PE
Type of contacts	Male (M) / Female (F)
Rated current I <sub>N</sub>	16 A
Rated voltage	400 V (EU)
Plug housing:	Plastic
Limit temperature	-40°... +80 °C
Pollution degree	3

Specification	Cable
Standard	DIN EN 50525-2-51
Designation	4G4
Bending radius	4x cable diameter
Outside diameter	approx. 10.9 mm
Insulation material	PVC
Conductor mat. / type	Cu, blanc / Finely stranded
Cable ends	Each end with plug

**PIN assignment**

Potential	PIN assignment Electronics Power OUT (Male)	Cable color: designation acc. to DIN VDE 0293	Potential	PIN assignment Electronics Power IN (Female)
L1	1	<b>Black: 1</b>	L1	1
L2	2	<b>Black: 2</b>	L2	2
L3	3	<b>Black: 3</b>	L3	3
	PE	<b>Green</b> <b>Yellow</b>		PE