



## IE3 or IE5+? A comparison in numbers

## **IE3** or **IE5+**? A comparison in numbers



IE3 asynchronous motor or IE5+ synchronous motor? In a drive system with a NORDAC ON frequency inverter and a NORD gear unit, both meet the requirements of warehouse logistics.

We have summarized the differences between the two motor types for you here, in addition to the different investment costs:

TYPE	MOTOR	DIMENSIONS	WEIGHT	EFFICIENCY* EN	NERGY CONSUMPTION
IEC 80 SP/4 (87 Hz)		276 mm	9.7 kg	75%	5.73 HPh 1717 HPh
1.27 HP		up to -17%	up to -28 %	+16 %	up to -11 %
IEC 71 F2/8 <b>IE5+</b> 1.34 HP		228 mm	7.0 kg	91 %	5.14 HPh 1540 HPh

## Our efficiency test was carried out under these conditions:

Operating hours: 16 h/day
Operating days: 6 days/week
Operating days: 300 days/year
Operating hours: 4800 h/year

<sup>\*</sup> Efficiency measured at 75 % speed and 50 % load